



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue  
75672-0000, TX Marshall  
Phone: 903-935-9535  
Fax: 903-935-3490



## S21345 5.5 Watt T10 Led; Clear; Medium

Satco

Catalog Number	S21345
Manufacturer	Satco
Description	5.5 Watt T10 Led Lamp - Clear - Medium Base - 90 Cri - 3000K - 120 Volts
Weight per unit	0.1290 (lbs/each)
Product Category	20221005122256

### Features

average life	15000
Base	E26
beam angle	300
dimnable	Yes-Dimmable
lumens	450
Power Factor	0.75
Shape	T10
Voltage Rating	120
Wattage	5.5

### Material, Color, and Finish

color rendering index (cri)	90+
color temperature	3000
Finish	Clear

### Dimensions and Weight

Size	5
------	---

### Descriptions

Description	5.5 WATT T10 LED; CLEAR; MEDIUM
extra long description	SATCO S21345 5.5T10/LED/CL/930/120V
Long Description	5.5 Watt T10 LED Lamp - Clear - Medium Base - 90 CRI - 3000K - 120 Volts
Product Type	5.5T10/Led/CL/930/120V/E26
Special Features	Warranty: 2-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +45C (+113F) ; Dimmable Text: 120V only ; Material: Glass / Nickel Plated Aluminum ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Soft White ; Efficacy: 81.82 LPW ; DLC Approved: False ; FCC Compliant: True ; NSF Approved: No ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED Filament ; ANSI Base: E26 ; Amps: 0.062A



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue  
75672-0000, TX Marshall  
Phone: 903-935-9535  
Fax: 903-935-3490

## Manufacturer Information

Brand	Satco
GTIN	00045923206528
Manufacturers Part Number	S21345
UPC	045923206528

## Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	LED General Service

## Packaging

Carton	1
Weight Per each	0.129

## Uses, Certifications, and Standards

Application	LED
standard	cULus - Certified;cULus - Listed