



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S21601 6" 13/16/19W Led Comm DNLT 27/30/35/40/50K

Satco

Catalog Number	S21601
Manufacturer	Satco
Description	18.5W Field Selectable Led 6-Inch Commercial Downlight - Dual Dimming - Round - 120-347 Volt
Weight per unit	1.4 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.154 to 0.053/0.131 to 0.045/0.110 to 0.038
Lamp Included	Integrated
Lamp Type	LED
Material	Aluminum
Socket Type	Integrated
Voltage Rating	120 to 347 V
Wattage	18.5/15.7/13.2

Material, Color, and Finish

Color	White
Style	Utility

Dimensions and Weight

Height	3.43
Length	7.4
Width	7.4

Descriptions

Description	6" 13/16/19W LED COMM DNLT 27/30/35/40/50K
extra long description	SATCO S21601 18.5W/CDL/6/120-347/FS
Long Description	18.5W Field Selectable LED 6-Inch Commercial Downlight - Dual Dimming - Round - 120-347 Volt
Product Type	18.5W/CDL/6/120-347/FS/RND/DD
Special Features	ADA Compliant: False;Amps: 0.154-0.053/0.131-0.045/0.110-0.038A;Beam Angle (degree): 105;Bulb Included: Integrated;Cct Selectable: True;Color Temp: Warm White to Natural Light;Fluor Equiv: 32W;Incandescent Equivalent: 100W;Indoor Outdoor: Indoor;IP Rating: IP20;JA8 Compliant: True;Lens Material: Polycarbonate (PC);Location Rating: Damp;Mounting Procedure: Ceiling;NSF Approved: No;Operating Frequency: 60Hz;Operating Temp: -20C (-4F) to +40C (+104F);Power Factor: >0.9;Replaceable Light Source: False;Style: U



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923411168
Manufacturers Part Number	S21601
UPC	045923411168

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	RECESSED LIGHTING

Packaging

Carton	1
Weight Per each	1.38

Uses, Certifications, and Standards

Application	Recessed
Frequency Rating	60 Hz
Mounting	CEILING
standard	cETLus - Listed