



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S21602 8" 17/23/26W Led Commercial DNLT 27K/3K/35K/4K/5K

Satco

Catalog Number	S21602
Manufacturer	Satco
Description	25.5W Field Selectable Led 8-Inch Commercial Downlight - Dual Dimming - Round - 120-347 Volt
Weight per unit	2.1 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.213 to 0.073/0.188 to 0.065/0.143 to 0.050
Lamp Included	Integrated
Lamp Type	LED
Material	Aluminum
Socket Type	Integrated
Voltage Rating	120 to 347 V
Wattage	25.5/22.5/17.2

Material, Color, and Finish

Color	White
Style	Utility

Dimensions and Weight

Height	4.02
Length	9.76
Width	9.76

Descriptions

Description	8" 17/23/26W LED COMMERCIAL DNLT 27K/3K/35K/4K/5K
extra long description	SATCO S21602 25.5W/CDL/8/120-347/FS
Long Description	25.5W Field Selectable LED 8-Inch Commercial Downlight - Dual Dimming - Round - 120-347 Volt
Product Type	25.5W/CDL/8/120-347/FS/RND/DD
Special Features	ADA Compliant: False;Amps: 0.213-0.073/0.188-0.065/0.143-0.050A;Beam Angle (degree): 100;Bulb Included: Integrated;Cct Selectable: True;Color Temp: Warm White to Natural Light;Fluor Equiv: 2 x 26W CFL;Incandescent Equivalent: 125W;Indoor Outdoor: Indoor;IP Rating: IP20;JA8 Compliant: True;Lens Material: Polycarbonate (PC);Location Rating: Damp;Mounting Procedure: Ceiling;NSF Approved: No;Operating Frequency: 60Hz;Operating Temp: -20C (-4F) to +40C (+104F);Power Factor: >0.9;Replaceable Light Source: False;



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923411175
Manufacturers Part Number	S21602
UPC	045923411175

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	RECESSED LIGHTING

Packaging

Carton	1
Package	4
Weight Per each	2.13

Uses, Certifications, and Standards

Application	Recessed
Frequency Rating	60 Hz
Mounting	CEILING
standard	cETLus - Listed