



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S40502GR00 1/2" SS304 Cord Grip .188-.250

Calbrite

| | |
|------------------|--------------------------------|
| Catalog Number | S40502GR00 |
| Manufacturer | Calbrite |
| Description | 1/2" SS304 Cord Grip .188-.250 |
| Weight per unit | 0.2300 (lbs/each) |
| Product Category | Cable & Cord Grips |

Features

| | |
|----------|-----------------------|
| Material | Stainless Steel - 304 |
|----------|-----------------------|

Material, Color, and Finish

| | |
|--------|--------------------|
| Color | Polished Silver |
| Finish | #4 Polished Finish |

Dimensions and Weight

| | |
|--------|------|
| Length | 1.8 |
| Width | 1.25 |

Descriptions

| | |
|------------------------|--|
| Description | 1/2" SS304 CORD GRIP .188-.250 |
| extra long description | CAL S40502GR00 1/2 SS304 CGRIP .188 |
| Features | Stainless steel cord grips completely eliminate pull tension on terminals, control cable arc-of-bend, prevent cord pull-out, and provide a liquid-tight seal. All connectors can be ordered with or without wire mesh attachments and accommodate conduit sizes from 1/2" to 2". |
| Long Description | 1/2" SS304 CORD GRIP .188-.250 |
| Product Type | 1/2 SS304 Cgrip .188-.250 |
| Short Description | SS_CRD GRP_304 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | CALBRITE |
| GTIN | 00847656012519 |
| Manufacturers Part Number | S40502GR00 |
| UPC | 847656012519 |

Taxonomies, Classifications, and Categories

| | |
|------|-----------|
| Type | CONNECTOR |
|------|-----------|

Trade Size

| | |
|------------|-----|
| Trade Size | 1/2 |
|------------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|----------------------|-----------|
| Carton..... | 1..... |
| Weight..... | 0.23..... |
| Weight Per foot..... | 0.23..... |

Uses, Certifications, and Standards

| | |
|-------------------------|----------|
| Temperature Rating..... | 250..... |
|-------------------------|----------|