



S5860

MP150/ED17/U/PS
150 watt; Metal Halide HID; Medium base; ED17; Clear; 65
CRI; 4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start
- Open Rated



S5860

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|---------------|---------------|---------------------|------------------|----------------|------------|-----------------|
| S5860 | 045923058608 | 150 | ED17 | Medium | E26 | M102/O | MP150/ED17/U/PS |
| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color | Pulse Start |
| Clear | 5.44" | 2.13" | 10000 | 14000 | 4000 | Cool White | Yes |
| Open Rated | Pack | Package Type | CRI | Burning Position | RoHS Compliant | | |
| Yes | 12 | Box | 65 | Universal | Yes | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S5860

MP150/ED17/U/PS
150 watt; Metal Halide HID; Medium base; ED17; Clear; 65
CRI; 4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start
- Open Rated



S5860

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|---------------|---------------|---------------------|------------------|----------------|------------|-----------------|
| S5860 | 045923058608 | 150 | ED17 | Medium | E26 | M102/O | MP150/ED17/U/PS |
| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color | Pulse Start |
| Clear | 5.44" | 2.13" | 10000 | 14000 | 4000 | Cool White | Yes |
| Open Rated | Pack | Package Type | CRI | Burning Position | RoHS Compliant | | |
| Yes | 12 | Box | 65 | Universal | Yes | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

