

Project Name

Location

Prepared By



## SATCO S29816

15A19/LED/3000K/1600L/120V/D

**Notes**

(www) 12-30-2024 09:00:46

**General**

Status	Active
Watts	15W
Incandescent Equivalent	100W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	3000K
Temperature	Warm White
CRI	80
Lumens	1600L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Type A
Technology	LED

**Electrical**

Operating Frequency	60Hz
Power Factor	0.94
Operating Temperature	-25C (-13F) to +45C (+113F)

**Physical**

MOL	4.646
MOD	2.362
Weight (lb.)	0.11

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

**Compliance**

Safety Listing	cULus - Certified; cULus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2307666
CA T20 / T24 Rationale	Non-Compliant - <82 CRI
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
California Compliant Substitute	S28653
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Project Name

Location

Prepared By



## SATCO S29816

15A19/LED/3000K/1600L/120V/D

**Notes**

(www) 12-30-2024 09:00:46

**General**

Status	Active
Watts	15W
Incandescent Equivalent	100W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	3000K
Temperature	Warm White
CRI	80
Lumens	1600L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Type A
Technology	LED

**Electrical**

Operating Frequency	60Hz
Power Factor	0.94
Operating Temperature	-25C (-13F) to +45C (+113F)

**Physical**

MOL	4.646
MOD	2.362
Weight (lb.)	0.11

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

**Compliance**

Safety Listing	cULus - Certified; cULus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2307666
CA T20 / T24 Rationale	Non-Compliant - <82 CRI
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
California Compliant Substitute	S28653
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp