



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S3713BK Recept Recessed 15A/125V BK W/Wallplate

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | S3713BK |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Clock Hanger Recessed Receptacle With Smooth Wall Plate 15A, 125V, Gray |
| Weight per unit | 0.2760 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|--------------------|
| amperage rating | 15 |
| indoor/outdoor | Indoor |
| media | Yes |
| Number of Wires | 3 |
| Outlet Type | Commercial, Indoor |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 14 - 10 |

Dimensions and Weight

| | |
|------|----|
| Size | 5" |
|------|----|

Descriptions

| | |
|------------------------|---|
| Description | RECP RECESSED 15A/125V BK W/WALLPLATE |
| extra long description | P&S S3713BK RECEPT RECESSED 15A/125 |
| Long Description | Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V, Gray |
| Product Type | Recept Recessed 15A/125V BK W/Plate |
| Special Features | Dust & moisture resistant, clock hanger receptacle, cellular neoprene sealing mat fits under wall plate |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007687811 |
| Manufacturers Part Number | S3713-BK |
| UPC | 785007687811 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.276 |

Uses, Certifications, and Standards

| | |
|-------------|---------------|
| Application | Commercial |
| Mounting | WALL |
| nema rating | 5-15R |
| standard | CULUS, UL 498 |