



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2000 S. Bickley Ave.
79772-0000, TX Pecos
Phone: 432-445-1472
Fax: 432-445-1474



S41510CT00 1-1/2" SS304 Rigid Conduit, 10' W/Coupling

Cablofil

Catalog Number	S41510CT00
Manufacturer	Cablofil
Description	Stainless Steel Rigid Conduit, 304/316 Stainless Steel Material; Bright Polished Finish; 10 Foot; 1.61 Inch Inner Diameter; 1.9 Inch Outer Diameter; UL (Canada and US), Cul, Csa C22.1 Approval; Ansi 169, Nec, Nfpa 70 Applicable Standard
Weight per unit	2.6 (lbs/each)
Product Category	Galvanized Heavy Wall Conduit

Features

Applicable Standard	ANSI 169, NEC, NFPA 70
End Style	Threaded
Material	304/316 Stainless Steel

Material, Color, and Finish

Finish	Bright Polished
--------	-----------------

Dimensions and Weight

Inner Diameter	1.61 Inch
Length	10 Foot
Outer Diameter	1.9 Inch

Descriptions

Additional Information	Includes Coupling; Thread Size 11.5 TPI
Commodity Description	Galvanized Rigid Steel Conduit
Description	1-1/2" SS304 RIGID CONDUIT, 10' W/COUPLING
extra long description	304/316 STAINLESS STEEL MATERIAL; BRIGHT POLISHED FINISH; 10 FOOT; 1.61 INCH INNER DIAMETER; 1.9 INCH OUTER DIAMETER; UL (CANADA AND US), CUL, CSA C22.1 APPROVAL; ANSI 169, NEC, NFPA 70 APPLICABLE STANDARD; 2.63 POUND PER FOOT WEIGHT; 1-1/2 INCH TRADE SIZE; THREADED END STYLE; CALBRITE BRAND; INCLUDES COUPLING; THREAD SIZE 11.5 TPI
Long Description	STAINLESS STEEL RIGID CONDUIT, 304/316 STAINLESS STEEL MATERIAL; BRIGHT POLISHED FINISH; 10 FOOT; 1.61 INCH INNER DIAMETER; 1.9 INCH OUTER DIAMETER; UL (CANADA AND US), CUL, CSA C22.1 APPROVAL; ANSI 169, NEC, NFPA 70 APPLICABLE STANDARD
Product Type	Stainless Steel Rigid Conduit



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2000 S. Bickley Ave.
79772-0000, TX Pecos
Phone: 432-445-1472
Fax: 432-445-1474

Manufacturer Information

Brand	CALBRITE
GTIN	00847656000059
Manufacturers Part Number	S41510CT00
UPC	847656000059

Taxonomies, Classifications, and Categories

Category Description	Stainless Rigid Conduit
----------------------	-------------------------

Trade Size

Trade Size	1-1/2 INCH
------------	------------

Availability

Status	Inactive
--------	----------

Packaging

Carton	10
Weight	2.63 Pound per Foot
Weight Per each	2.63

Uses, Certifications, and Standards

Approval	UL (Canada and US), CUL, CSA C22.1
----------	------------------------------------