



S7376

105T5/41
105 watt; T5 Compact Fluorescent; 4100K; 85 CRI; Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7376

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|--------------|---------------|-------------------------------|----------------|-------------------------|------------------|--------------------------------|-----------|
| S7376 | 045923073762 | 120 | 105 | 400W | T5 | Medium | E26 |
| Lamp Code | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 105T5/41 | 10-3/4" | 4.31" | 7000 | 10000 | 4100 | Cool White | 12/6 |
| Package Type | CRI | CEC Status | Hg Content | RoHS Compliant | UL or ETL Listed | Warranty | |
| Box | 85 | Lawful for sale in California | 4.8 mg | Yes | Yes | 2 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S7376

105T5/41
105 watt; T5 Compact Fluorescent; 4100K; 85 CRI; Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7376

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|--------------|---------------|-------------------------------|----------------|-------------------------|------------------|--------------------------------|-----------|
| S7376 | 045923073762 | 120 | 105 | 400W | T5 | Medium | E26 |
| Lamp Code | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 105T5/41 | 10-3/4" | 4.31" | 7000 | 10000 | 4100 | Cool White | 12/6 |
| Package Type | CRI | CEC Status | Hg Content | RoHS Compliant | UL or ETL Listed | Warranty | |
| Box | 85 | Lawful for sale in California | 4.8 mg | Yes | Yes | 2 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

