



# S9622

9.5BR30/LED/4000K/830L/120V/D  
9.5 watt; BR30 LED; 105° beam spread; 4000K; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9622

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9622	DiTTO™	045923096228	120	9.5	65W	0.91	BR30
Base	ANSI Base	Lamp Code	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
Medium	E26	9.5BR30/LED/4000K/830L/120V/D	Frosted	5 3/16"	3.75"	830	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	80	105	12/6	Box	ENERGY STAR	Yes
UL or ETL Listed	UL Classification	Warranty					
Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>					



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9622

9.5BR30/LED/4000K/830L/120V/D  
9.5 watt; BR30 LED; 105° beam spread; 4000K; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9622

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9622	DiTTO™	045923096228	120	9.5	65W	0.91	BR30
Base	ANSI Base	Lamp Code	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
Medium	E26	9.5BR30/LED/4000K/830L/120V/D	Frosted	5 3/16"	3.75"	830	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	80	105	12/6	Box	ENERGY STAR	Yes
UL or ETL Listed	UL Classification	Warranty					
Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>					



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

