

## Ceiling Receptacle Lampholders

Medium Base  
660W, 125V/AC; 660W, 250V/AC  
600W, 250V/AC

### FEATURES

- Mounts on 4" (101.6mm) outlet boxes with breakout for 3.25" (82.5mm) box mounting.
- Leads are 6" (152.4mm) 221°F (105°C) insulated stranded #16 AWG, stripped 0.75" (19.0mm).
- Top wire versions have terminal screws backed out – ready for wiring – without removing interior.
- Push wire terminals are top wired with two push-in terminals and two screw terminals for continuous wiring.
- Pull chain devices include ball chain, 3' (0.9m) of cord, connector and end bell.
- Porcelain models made of high-strength insulator porcelain; pull chain versions feature removable interiors.
- Plastic models made with high-temperature thermoset plastic to reduce breakage.



667

### Porcelain Ceiling Lampholders

660W 125V/AC or 660W 250V/AC; Top Wire

Description	Color	Catalog No.
125V Two-Piece, with 15A 125V/AC NEMA 1-15P 2P, 2W Outlet 2 Screw Terminals, Pull Chain Switch	White	<input type="checkbox"/> 669
125V Two-Piece, with 15A 125V/AC NEMA 5-15P 2P, 3W Outlet 2 Screw Terminals, Pull Chain Switch	White	<input type="checkbox"/> 667
250V One-Piece, with Feed-Through 4 Screw Terminals, Keyless Switch	White	<input type="checkbox"/> 604
250V Two-Piece, with Feed-Through 4 Screw Terminals, Pull Chain Switch	White	<input type="checkbox"/> 659



669

cULus Listed to UL 496, file no. E7430; NOM certified



S788W

### Plastic Ceiling Lampholders

600W 250V/AC or 660W 250V/AC

Description	Color	Catalog No.	
600W Two-Piece, Push Wire/Top Wire, Pull Chain Switch	White	<input type="checkbox"/> S759W-CD	
600W Two-Piece, 6" (152.4mm) Wire Leads, Pull Chain Switch	White	<input type="checkbox"/> S788W	
660W Two-Piece, with 15A 125V/AC NEMA 1-15P 2P, 2W Outlet Push Wire/Top Wire, Pull Chain Switch	White	<input type="checkbox"/> S860W	
660W Two-Piece, with 15A 125V/AC NEMA 5-15P 2P, 3W Outlet Push Wire/Top Wire, Pull Chain Switch	White	<input type="checkbox"/> S865W	
660W One-Piece, 4 Top Wire Screws, Keyless Switch	White	<input type="checkbox"/> S1174W	•
660W One-Piece, 6" (152.4mm) Wire Leads, Keyless Switch	White	<input type="checkbox"/> S1174-6W	•
660W Two-Piece, Push Wire/Top Wire, Keyless Switch	White	<input type="checkbox"/> S768W	
660W Two-Piece, 6" (152.4mm) Wire Leads, Keyless Switch	White	<input type="checkbox"/> S768-6W	



S1174W

cULus Listed to UL 496, file no. E7430; NOM certified

**Dimensional Information:** B-63

**Specification Information:** Please visit [www.cooperwiringdevices.com](http://www.cooperwiringdevices.com)

**NAFTA Compliant:** See page F-21