



S8667

FT40HL/835 /RS /ENV
40 watt; pin-based Compact Fluorescent; 3500K; 82 CRI; 2G11 base

Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8667

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|----------------|----------------|---------------------|-------------|---------------|-----------|---------------------|---------|
| S8667 | 045923086670 | 40 | T5 | 2G11 | 2G11 | FT40HL/835 /RS /ENV | 120 |
| MOL In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack | Package Type | CRI |
| 22.5 | 3500 | 20000 | 3500 | Neutral White | 10 | Box | 82 |
| RoHS Compliant | | | | UL Listed | | | |
| Yes | | | | Yes | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8667

FT40HL/835 /RS /ENV
40 watt; pin-based Compact Fluorescent; 3500K; 82 CRI; 2G11 base

Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8667

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|----------------|----------------|---------------------|-------------|---------------|-----------|---------------------|---------|
| S8667 | 045923086670 | 40 | T5 | 2G11 | 2G11 | FT40HL/835 /RS /ENV | 120 |
| MOL In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack | Package Type | CRI |
| 22.5 | 3500 | 20000 | 3500 | Neutral White | 10 | Box | 82 |
| RoHS Compliant | | | | UL Listed | | | |
| Yes | | | | Yes | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

