

Eaton SFDN100

Catalog Number: SFDN100

Eaton Circuit Breaker Enclosure, 15-100A, Series C, NEMA 1, EHD, FD, FDB, HFD, Surface



General specifications

Product Name	Catalog Number
Eaton enclosed circuit breaker	SFDN100
UPC	Product Length/Depth
786679257159	19.5 in
Product Height	Product Width
6.75 in	14.1 in
Product Weight	Warranty
11.4 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed CSA Certified	With Knockouts

Product specifications

Type

Circuit Breaker Enclosure

Amperage Rating

15-100A

Circuit breaker type

EHD, FD, FDB, HFD

Enclosure

NEMA 1

Series

Series C

Mounting Method

Surface mounting

Resources

Specifications and datasheets

[Eaton Specification Sheet - SFDN100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton SFDN100

Catalog Number: SFDN100

Eaton Circuit Breaker Enclosure, 15-100A, Series C, NEMA 1, EHD, FD, FDB, HFD, Surface



General specifications

Product Name	Catalog Number
Eaton enclosed circuit breaker	SFDN100
UPC	Product Length/Depth
786679257159	19.5 in
Product Height	Product Width
6.75 in	14.1 in
Product Weight	Warranty
11.4 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed CSA Certified	With Knockouts

Product specifications

Type

Circuit Breaker Enclosure

Amperage Rating

15-100A

Circuit breaker type

EHD, FD, FDB, HFD

Enclosure

NEMA 1

Series

Series C

Mounting Method

Surface mounting

Resources

Specifications and datasheets

[Eaton Specification Sheet - SFDN100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia