

Eaton SFDN225

Catalog Number: SFDN225

Eaton enclosed circuit breaker, 125-225A, Series C, NEMA 1, FD, FDB, HFD, FDC, ED, EDH, EDC, FDC (15-225A), Surface



General specifications

Product Name	Catalog Number
Eaton enclosed circuit breaker	SFDN225
UPC	Product Length/Depth
786679002339	6.28 in
Product Height	Product Width
23.25 in	8.56 in
Product Weight	Warranty
15 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed CSA Certified	With knockouts.

Product specifications

Type

Circuit Breaker Enclosure

Amperage Rating

125-225A

Circuit breaker type

FD, FDB, HFD, FDC, ED, EDH, EDC, FDC

Enclosure

NEMA 1

Series

Series C

Mounting Method

Surface mounting

Resources

Brochures

[Customized Solutions - Customized Service](#)

Drawings

[SFDN225 Circuit Breaker Enclosure - Drawing](#)

Specifications and datasheets

[Eaton Specification Sheet - SFDN225](#)

[Enclosed Circuit Breakers - Technical Data](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton SFDN225

Catalog Number: SFDN225

Eaton enclosed circuit breaker, 125-225A, Series C, NEMA 1, FD, FDB, HFD, FDC, ED, EDH, EDC, FDC (15-225A), Surface



General specifications

Product Name	Catalog Number
Eaton enclosed circuit breaker	SFDN225
UPC	Product Length/Depth
786679002339	6.28 in
Product Height	Product Width
23.25 in	8.56 in
Product Weight	Warranty
15 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed CSA Certified	With knockouts.

Product specifications

Type

Circuit Breaker Enclosure

Amperage Rating

125-225A

Circuit breaker type

FD, FDB, HFD, FDC, ED, EDH, EDC, FDC

Enclosure

NEMA 1

Series

Series C

Mounting Method

Surface mounting

Resources

Brochures

[Customized Solutions - Customized Service](#)

Drawings

[SFDN225 Circuit Breaker Enclosure - Drawing](#)

Specifications and datasheets

[Eaton Specification Sheet - SFDN225](#)

[Enclosed Circuit Breakers - Technical Data](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia