

# Eaton SFDN225

Catalog Number: SFDN225

Eaton enclosed circuit breaker, 125-225A, Series C, NEMA 1, FD, FDB, HFD, FDC, ED, EDH, EDC, FDC (15-225A), Surface



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton enclosed circuit breaker	SFDN225
<b>UPC</b>	<b>Product Length/Depth</b>
786679002339	6.28 in
<b>Product Height</b>	<b>Product Width</b>
23.25 in	8.56 in
<b>Product Weight</b>	<b>Warranty</b>
15 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	With knockouts.

## Product specifications

### Type

Circuit Breaker Enclosure

### Amperage Rating

125-225A

### Circuit breaker type

FD, FDB, HFD, FDC, ED, EDH, EDC, FDC

### Enclosure

NEMA 1

### Series

Series C

### Mounting Method

Surface mounting

## Resources

### Catalogs

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

### Specifications and datasheets

[Eaton Specification Sheet - SFDN225](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton SFDN225

Catalog Number: SFDN225

Eaton enclosed circuit breaker, 125-225A, Series C, NEMA 1, FD, FDB, HFD, FDC, ED, EDH, EDC, FDC (15-225A), Surface



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton enclosed circuit breaker	SFDN225
<b>UPC</b>	<b>Product Length/Depth</b>
786679002339	6.28 in
<b>Product Height</b>	<b>Product Width</b>
23.25 in	8.56 in
<b>Product Weight</b>	<b>Warranty</b>
15 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	With knockouts.

## Product specifications

### Type

Circuit Breaker Enclosure

### Amperage Rating

125-225A

### Circuit breaker type

FD, FDB, HFD, FDC, ED, EDH, EDC, FDC

### Enclosure

NEMA 1

### Series

Series C

### Mounting Method

Surface mounting

## Resources

### Catalogs

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

### Specifications and datasheets

[Eaton Specification Sheet - SFDN225](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)