

# Specifications



## Eaton SFDN100

Eaton Circuit Breaker Enclosure, 15-100A, Series C, NEMA 1, EHD, FD, FDB, HFD, Surface

### General specifications

<b>PRODUCT NAME</b>	Eaton enclosed circuit breaker
<b>CATALOG NUMBER</b>	SFDN100
<b>UPC</b>	786679257159
<b>PRODUCT LENGTH/DEPTH</b>	19.5 in
<b>PRODUCT HEIGHT</b>	6.75 in
<b>PRODUCT WIDTH</b>	14.1 in
<b>PRODUCT WEIGHT</b>	11.4 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	With Knockouts

## Product specifications

<b>AMPERAGE RATING</b>	15-100A
<b>CIRCUIT BREAKER TYPE</b>	EHD, FD, FDB, HFD
<b>ENCLOSURE</b>	NEMA 1
<b>SERIES</b>	Series C
<b>MOUNTING METHOD</b>	Surface mounting
<b>TYPE</b>	Circuit Breaker Enclosure

## Resources

### CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - SFDN100](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton SFDN100

Eaton Circuit Breaker Enclosure, 15-100A, Series C, NEMA 1, EHD, FD, FDB, HFD, Surface

### General specifications

<b>PRODUCT NAME</b>	Eaton enclosed circuit breaker
<b>CATALOG NUMBER</b>	SFDN100
<b>UPC</b>	786679257159
<b>PRODUCT LENGTH/DEPTH</b>	19.5 in
<b>PRODUCT HEIGHT</b>	6.75 in
<b>PRODUCT WIDTH</b>	14.1 in
<b>PRODUCT WEIGHT</b>	11.4 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	With Knockouts

## Product specifications

<b>AMPERAGE RATING</b>	15-100A
<b>CIRCUIT BREAKER TYPE</b>	EHD, FD, FDB, HFD
<b>ENCLOSURE</b>	NEMA 1
<b>SERIES</b>	Series C
<b>MOUNTING METHOD</b>	Surface mounting
<b>TYPE</b>	Circuit Breaker Enclosure

## Resources

### CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - SFDN100](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

