



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SKAB250 250MCM Al/Cu Butt Splice

Nsi Industries

| | |
|------------------|--|
| Catalog Number | SKAB250 |
| Manufacturer | Nsi Industries |
| Description | Easy-Splice Dual Rated Direct Burial Butt Splice Kit For 1/0 Awg to 250 MCM Utilizing A Mechanical Dual Rated Splice and Matched Heavy Wall Heat Shrink Tubing to Create An Insulated Splice For Copper and/or Aluminum Cables. Temperature Rating: 105 Degrees C. 600 Volt Maximum. |
| Weight per unit | 0.3760 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

Features

| | |
|----------------|-----------------|
| Cable Size | 1/0 AWG-250 MCM |
| Cable Type | Class A-B |
| insulation | Heat Shrink |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Descriptions

| | |
|------------------------|--|
| Description | 250MCM AL/CU BUTT SPLICE |
| extra long description | NSI SKAB-250 Easy Splice ALCU Butt |
| Features | Easy-Splice Dual Rated Direct Burial Butt Splice Kit for 1/0 AWG to 250 MCM Utilizing a mechanical dual rated splice and matched heavy wall heat shrink tubing to create an insulated splice for copper and/or aluminum cables. Temperature Rating: 105 degrees C. 600 Volt Maximum. |
| Long Description | Easy-Splice Dual Rated Direct Burial Butt Splice Kit for 1/0 AWG to 250 MCM Utilizing a mechanical dual rated splice and matched heavy wall heat shrink tubing to create an insulated splice for copper and/or aluminum cables. Temperature Rating: 105 degrees C. 600 Volt Maximum. |
| Product Type | Easy Splice Alcu Butt Splice 250 |
| Special Features | Dual Rated For Use With Copper And Aluminum Cable |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381169167 |
| Manufacturers Part Number | SKAB-250 |
| UPC | 662381169167 |

Taxonomies, Classifications, and Categories

| | |
|------|---|
| Type | Direct Burial Splice Kit With Heat Shrink |
|------|---|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 0.376 |

Uses, Certifications, and Standards

| | |
|-----------------------|---------------|
| Application | Splicing Wire |
| Operating Temperature | -40 C To 90 C |