



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SPM25L 2, #2 Service Post Connector 3/8 X 1-1/8 *Nsi Industries*

Catalog Number	SPM25L
Manufacturer	Nsi Industries
Description	Service Post Connector - Two Wire Type 10- 2 Awg Service Post Connectors Is Used For Connecting One or Two Conductors. Made From High Copper Content Hard-Drawn Rod. Lay-In Feature Makes Them Excellent For Continuous Loop Grounding and Bonding. Used to Ground to Bar or Plate. Suitable For Direct Burial In Earth or Concrete.
Weight per unit	0.3600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	10 SOL - 2 STR
Wire Type	Class A & B

Material, Color, and Finish

Color	Copper
Finish	COPPER

Dimensions and Weight

Size	Stud=3/8 x 16-1 1/8 - Hex Nut=5/8 x 18
------	----------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	2, #2 SERVICE POST CONNECTOR 3/8 X 1-1/8
extra long description	NSI SPM-25L Service Post Two Wire 1
Features	Service Post Connector - Two Wire Type 10- 2 AWG Service Post Connectors is used for connecting one or two conductors. Made from high copper content hard-drawn rod. Lay-in feature makes them excellent for continuous loop grounding and bonding. Used to ground to bar or plate. Suitable for direct burial in earth or concrete.
Long Description	Service Post Connector - Two Wire Type 10- 2 AWG Service Post Connectors is used for connecting one or two conductors. Made from high copper content hard-drawn rod. Lay-in feature makes them excellent for continuous loop grounding and bonding. Used to ground to bar or plate. Suitable for direct burial in earth or concrete.
Product Type	Service Post Two Wire 10-2 Awg
Special Features	10 SOL-2 STR - 12 Pack

Manufacturer Information

Brand	NSi
GTIN	00662381021144
Manufacturers Part Number	SPM-25L
UPC	662381021144

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Service Post Connectors

Packaging

Carton	12
Weight Per each	0.36

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B
Temperature Rating	90 C