# Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685




## SS403 3WAY In-Wall Dig TMR

*Nsi Industries*

| | |
|---|---|
| Catalog Number | SS403 |
| Manufacturer | Nsi Industries |
| Description | Interval Timer 24 HR 120-277V White |
| Weight per unit | 0.3900 (lbs/each) |
| Product Category | Electronic Time Switches |

## Features

| | |
|---|---|
| action | SPST |
| Base | Screw |
| Contact Rating | 120-230-277 VAC |
| Phase | Single Phase |
| Poles | 1 |
| Timing Range | 7 DAY |

## Dimensions and Weight

| | |
|---|---|
| Size | H=5.00 - W=3.00 |

## Descriptions

| | |
|---|---|
| Description | 3WAY IN-WALL DIG TMR |
| extra long description | TORK SS403 Interval Wall Timer 24 H |
| Features | Tork Digital Interval Timer w/o Neutral APPLICATIONS: Offices, Meeting Rooms, Energy Code Timed Override, Exhaust Fans, Equipment Rooms, Closets, Storage Spaces. FEATURES: COLOR: White (single gang decorator wall plate included) ENERGY CODE PRESET: 2 hour timing for Title 24 and IECC (default) 4 hour timing for ASHRAE 90.1 (with quick dip switch adjustment) PROGRAMMABLE: 5 minutes to 25 hour: 5 minute steps from 5 minutes to 1 hour 10 minute steps from 1 to 4 hours 30 minute steps from 4 to 12 hours 1 hour |
| Long Description | Interval Timer 24 Hr 120-277V White |
| Product Type | Interval Wall Timer 24 Hour Maximum No Neutral 3-Way 15A 120 |
| Special Features | White 7 Day In Wall Time Switch |

## Manufacturer Information

| | |
|---|---|
| Brand | Nsi Industries |
| GTIN | 00786261140296 |
| Manufacturers Part Number | SS403 |
| UPC | 786261140296 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | TIME CLOCKS |
| Type | Digital Auto Off In Wall Time Switch |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Weight Per each | 0.39 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | NSI |
| environmental conditions | 32 - + 104 F |
| Frequency Rating | 50-60 Hz |
| Mounting | Screw Mount |
| Operating Temperature | 32 - + 104 F |
| standard | cULus |