



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SSF248H0120VEB21 2 Lamp, 4' STN Industrial, High Output, Electronic *Cooper Lighting Solutions*

| | |
|------------------|--|
| Catalog Number | SSF248H0120VEB21 |
| Manufacturer | Cooper Lighting Solutions |
| Description | 2 Lamp, 4' High Output Standard Strip, Electronic T12, Flip-Up Sockets |
| Weight per unit | 12.0 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|---------------|
| amperage rating | 0.8 (at 120V) |
| Lamp Type | T12 |
| lumens | N/A |
| Voltage Rating | 120V |
| Wattage | 96W |

Dimensions and Weight

| | |
|------|--|
| Size | 48.938 IN Length 5.0 IN Width 2.75 IN Height |
|------|--|

Descriptions

| | |
|------------------------|--|
| Description | 2 LAMP, 4' STN INDUSTRIAL, HIGH OUTPUT, ELECTRONIC |
| extra long description | CLS SSF-248HO-120V-EB21-U SSF 2 LMP |
| Long Description | 2 Lamp, 4' High Output Standard Strip, Electronic T12, Flip-up Sockets |
| Product Type | SSF 2 LMP 4' Wide HGH Opt STRP Elt T12 |
| Special Features | Flip-up socket feature for faster installation out of the box |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | Eaton Lighting |
| GTIN | 00080083519491 |
| Manufacturers Part Number | SSF-248HO-120V-EB21-U |
| UPC | 080083519491 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | Fluorescent Fixtures & Accessories |
| Type | Strip |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 12 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-------------------------------|
| Application | lighting |
| Mounting | Strip |
| standard | UL/cUL Listed - Damp Location |