

Specifications



Eaton STE8W

Eaton Sectional wallplate, Wallplate, White, Duplex receptacle, Cutout, Polycarbonate, Single- gang, Mid-size, End piece

General specifications

PRODUCT NAME	Eaton sectional wallplate
CATALOG NUMBER	STE8W
UPC	032664578540
PRODUCT LENGTH/DEPTH	0.08 in
PRODUCT HEIGHT	4.87 in
PRODUCT WIDTH	3.12 in
PRODUCT WEIGHT	0.048 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed UL Listed



Product specifications

SPECIAL FEATURES	End piece
TYPE	Wallplate
CUTOUT	Duplex receptacle
WALLPLATE SIZE	Mid-size

Resources

CATALOGS	Arrow Hart Buyer Guide Section K
MULTIMEDIA	Wiring devices wallplates

COLOR	White
NUMBER OF GANGS	1
MATERIAL	Polycarbonate

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - STE8W
-------------------------------	---

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Eaton STE8W

Eaton Sectional wallplate, Wallplate, White, Duplex receptacle, Cutout, Polycarbonate, Single- gang, Mid-size, End piece

General specifications

PRODUCT NAME	Eaton sectional wallplate
CATALOG NUMBER	STE8W
UPC	032664578540
PRODUCT LENGTH/DEPTH	0.08 in
PRODUCT HEIGHT	4.87 in
PRODUCT WIDTH	3.12 in
PRODUCT WEIGHT	0.048 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed UL Listed



Product specifications

SPECIAL FEATURES	End piece
TYPE	Wallplate
CUTOUT	Duplex receptacle
WALLPLATE SIZE	Mid-size

Resources

CATALOGS	Arrow Hart Buyer Guide Section K
MULTIMEDIA	Wiring devices wallplates

COLOR	White
NUMBER OF GANGS	1
MATERIAL	Polycarbonate

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - STE8W
--------------------------------------	---

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

