

# Specifications

## Eaton T37 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, T shape, 1"



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	T37 SA
<b>UPC</b>	782274627151
<b>PRODUCT LENGTH/DEPTH</b>	7.25 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	2.25 in
<b>PRODUCT WEIGHT</b>	0.9 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	12

## Resources

### CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

### CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

### INSTALLATION INSTRUCTIONS

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

### SPECIFICATIONS AND DATASHEETS

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - T37 SA](#)

### TECHNICAL SERVICE BULLETINS

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

## Product specifications

<b>SHAPE</b>	T
<b>TRADE SIZE</b>	1"
<b>MATERIAL</b>	Copper-free aluminum

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton T37 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, T shape, 1"



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	T37 SA
<b>UPC</b>	782274627151
<b>PRODUCT LENGTH/DEPTH</b>	7.25 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	2.25 in
<b>PRODUCT WEIGHT</b>	0.9 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	12

## Resources

### CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

### CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

### INSTALLATION INSTRUCTIONS

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

### SPECIFICATIONS AND DATASHEETS

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - T37 SA](#)

### TECHNICAL SERVICE BULLETINS

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

## Product specifications

<b>SHAPE</b>	T
<b>TRADE SIZE</b>	1"
<b>MATERIAL</b>	Copper-free aluminum

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

