

Specifications

Eaton T37 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, T shape, 1"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	T37 SA
UPC	782274627151
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.25 in
PRODUCT WEIGHT	0.9 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Resources

CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

INSTALLATION INSTRUCTIONS

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - T37 SA](#)

TECHNICAL SERVICE BULLETINS

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

Product specifications

SHAPE	T
TRADE SIZE	1"
MATERIAL	Copper-free aluminum

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton T37 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, T shape, 1"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	T37 SA
UPC	782274627151
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.25 in
PRODUCT WEIGHT	0.9 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Resources

CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

INSTALLATION INSTRUCTIONS

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - T37 SA](#)

TECHNICAL SERVICE BULLETINS

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

Product specifications

SHAPE	T
TRADE SIZE	1"
MATERIAL	Copper-free aluminum

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

