



## TRADEMASTER TOGGLE DIMMER, LIGHT ALMOND

T600LA | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Toggle Dimmer 600watt 1pole Light Almond



- Tough, impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Product Series: TradeMaster  
Type: Incandescent Toggle  
Number Of Poles: 1  
Style: Toggle

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121502  
UR: No

## DIMENSIONS

Weight: 0.23406

## TECHNICAL INFORMATION

Volts: 120V

Watts: 600

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





## TRADEMASTER TOGGLE DIMMER, LIGHT ALMOND

T600LA | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Toggle Dimmer 600watt 1pole Light Almond



- Tough, impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Product Series: TradeMaster  
Type: Incandescent Toggle  
Number Of Poles: 1  
Style: Toggle

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121502  
UR: No

## DIMENSIONS

Weight: 0.23406

## TECHNICAL INFORMATION

Volts: 120V

Watts: 600

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

