



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10440 Airline Highway  
70816-0000, LA Baton Rouge  
Phone: 225-292-7746  
Fax: 225-292-7840



## **T67 2" T FM7 Cond Body** *Appleton/Oz Gedney*

Catalog Number	T67
Manufacturer	Appleton/Oz Gedney
Description	FM7 Unilets Type T Conduit Outlet Body, Hub Size: 2 In, Form: 7, Length: 9.19 In, Width: 4.13 In, Height: 3.13 In, Material: Grayloy-Iron, Finish: Triple-Coat (Zinc Electroplate, Chromate and Epoxy Powder Coat), Color: Gray, Connection: Taper
Weight per unit	6.0 (lbs/each)
Product Category	Bodies & Covers

### **Features**

connection	Tapered Female Threaded
Form	7

### **Material, Color, and Finish**

Color	Gray
Finish	Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coat)

### **Dimensions and Weight**

Height	3.13
Hub Size	2
Length	9.19
Width	4.13

### **Descriptions**

Description	2" T FM7 COND BODY
extra long description	APP T67 2 FM7 BODY
Long Description	FM7 UNILETS Type T Conduit Outlet Body, Hub Size: 2 IN, Form: 7, Length: 9.19 IN, Width: 4.13 IN, Height: 3.13 IN, Material: Grayloy-Iron, Finish: Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coat), Color: Gray, Connection: Taper
Product Type	2 FM7 Body (A)
Special Features	Accurately tapped, tapered threads for tight, rigid joints and excellent ground continuity;Allow connections for branch runs;Completely interchangeable with Crouse-Hinds Form 7 bodies, gaskets and covers;Connect and change direction of conduit runs;Equivalent FM7 and Form 7 units have identical applications and installation dimensions;Fits flush and snug against flat surfaces for more stable installation;Flat back design provides greater cubic content for easier wire pulling and more room for splicing;Hub



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10440 Airline Highway  
70816-0000, LA Baton Rouge  
Phone: 225-292-7746  
Fax: 225-292-7840

## Manufacturer Information

Brand	Appleton
GTIN	00781381507127
UPC	781381507127

## Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Type T Conduit Outlet Body

## Packaging

Carton	5
Weight Per each	6

## Uses, Certifications, and Standards

Application	For Use With Rigid Steel, Rigid Aluminum Conduit And IMC
standard	UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1