



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## T70BWH10 T70 Raceway Base

*Panduit Corporation*

Catalog Number	T70BWH10
Manufacturer	Panduit Corporation
Description	The T-70 Raceway Base Provides Solutions For Routing Low Voltage, Fiber Optic, and/or Power Cabling Along Perimeter Walls. The T-70 Raceway Is Supplied With Pre-Punched Mounting Holes and Is Tamper Resistant. It Is 10 FT and White.
Weight per unit	5.4 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

### Features

Cover Type	Multi-Channel
Material	Polyvinyl Chloride (PVC)
media	Yes

### Material, Color, and Finish

Color	White
-------	-------

### Dimensions and Weight

Height	1.77
Length	10
Width	4.07

### Descriptions

Description	T70 RACEWAY BASE
extra long description	PAN T70BWH10 Surface Raceway, T-70
Long Description	THE T-70 RACEWAY BASE PROVIDES SOLUTIONS FOR ROUTING LOW VOLTAGE, FIBER OPTIC, AND/OR POWER CABLING ALONG PERIMETER WALLS. THE T-70 RACEWAY IS SUPPLIED WITH PRE-PUNCHED MOUNTING HOLES AND IS TAMPER RESISTANT. IT IS 10 FT AND WHITE.
Product Type	Surface Raceway, T-70 Base, 10 FT, White

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983727377
Manufacturers Part Number	T70BWH10
UPC	074983727377

### Taxonomies, Classifications, and Categories

Category Description	WIRE DUCT AND COVERS
Type	T-70 Channel



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	60
Weight Per foot	5.4

## Uses, Certifications, and Standards

Application	Provides Solutions for Routing Low Voltage, Fiber Optic and/or Power Cabling Along Perimeter Walls.T-70 Features the Workstation Outlet Center™ Offset Box, Which Provides an Offset Solution to Maximize Channel Capacity and Outlet Density.
standard	CE Compliant, UL5A Listed, UL Listed 95425, UL Listed E116129