

Specifications



Eaton TCFH100N

Eaton Bussmann series TCFH modular fuse holder, Electrical panelboards, Machinery disconnects, Industrial control, Required finger safe systems, 100 A, Class CF, Glass filled PBT, Panel, 600 Vac/dc, Low-peak finger safe fuse

General specifications

PRODUCT NAME	Eaton Bussmann series TCFH modular fuse holder
CATALOG NUMBER	TCFH100N
UPC	051712223508
PRODUCT LENGTH/DEPTH	2.91 in
PRODUCT HEIGHT	2.1 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	0.25 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	Contact Manufacturer UL Listed



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	100 A
VOLTAGE RATING	600 Vac, 600 Vdc

General information

CLASS	Class CF
MOUNTING METHOD	Panel
USED WITH	low-peak finger safe fuse

Physical details

MATERIAL	Glass filled PBT
----------	------------------

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007
MULTIMEDIA	Bussmann series Fuseology The Power of Space
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TCFH100N
TECHNICAL DATA SHEETS	TCFH100N~CUBFUSE 100 AMP HOLDER HIGH PROFILE
TECHNICAL SERVICE BULLETINS	Datasheet - FNQ-30

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Eaton TCFH100N

Eaton Bussmann series TCFH modular fuse holder, Electrical panelboards, Machinery disconnects, Industrial control, Required finger safe systems, 100 A, Class CF, Glass filled PBT, Panel, 600 Vac/dc, Low-peak finger safe fuse

General specifications

PRODUCT NAME	Eaton Bussmann series TCFH modular fuse holder
CATALOG NUMBER	TCFH100N
UPC	051712223508
PRODUCT LENGTH/DEPTH	2.91 in
PRODUCT HEIGHT	2.1 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	0.25 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	Contact Manufacturer UL Listed



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	100 A
VOLTAGE RATING	600 Vac, 600 Vdc

General information

CLASS	Class CF
MOUNTING METHOD	Panel
USED WITH	low-peak finger safe fuse

Physical details

MATERIAL	Glass filled PBT
----------	------------------

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007
MULTIMEDIA	Bussmann series Fuseology The Power of Space
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TCFH100N
TECHNICAL DATA SHEETS	TCFH100N~CUBFUSE 100 AMP HOLDER HIGH PROFILE
TECHNICAL SERVICE BULLETINS	Datasheet - FNQ-30

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

