

Specifications

Eaton TCI254

Eaton strain relief dust tight grip, Insulated, 0.52-0.73" cord diameter, 3/4" fitting, NPT thread

General specifications

PRODUCT NAME	Eaton strain relief dust tight grip
CATALOG NUMBER	TCI254
UPC	040893646527
PRODUCT LENGTH/DEPTH	1.39 in
PRODUCT HEIGHT	10.2 in
PRODUCT WIDTH	1.39 in
PRODUCT WEIGHT	0.16 lb
CERTIFICATIONS	CSA Certified UL Listed
PRODUCT TYPE	Strain relief dust tight grip



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Insulated
TYPE	Strain relief dust tight grip
CORD DIAMETER	0.52-0.73 in
FITTING SIZE	3/4 in
THREAD TYPE	NPT

Resources

CATALOGS	Arrow Hart Buyers Guide Section N
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TC1254

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton TCI254

Eaton strain relief dust tight grip, Insulated, 0.52-0.73" cord diameter, 3/4" fitting, NPT thread

General specifications

PRODUCT NAME	Eaton strain relief dust tight grip
CATALOG NUMBER	TCI254
UPC	040893646527
PRODUCT LENGTH/DEPTH	1.39 in
PRODUCT HEIGHT	10.2 in
PRODUCT WIDTH	1.39 in
PRODUCT WEIGHT	0.16 lb
CERTIFICATIONS	CSA Certified UL Listed
PRODUCT TYPE	Strain relief dust tight grip



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Insulated
TYPE	Strain relief dust tight grip
CORD DIAMETER	0.52-0.73 in
FITTING SIZE	3/4 in
THREAD TYPE	NPT

Resources

CATALOGS	Arrow Hart Buyers Guide Section N
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TC1254

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

