



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TM870NICC10 Radiant Switch 1P 15A 120/277V Nickel *Pass & Seymour/Legrand*

Catalog Number	TM870NICC10
Manufacturer	Pass & Seymour/Legrand
Description	Nickeldecorator Switch, Single POLE15AMP, 120/277VAC With Ground, Side and, Back Wire. Our Complete Line Of Decorator Devices Combine Today'S Design Aesthetics With Ease Of Installation, Reliability, and Performance That Never Goes Out Of Style.
Weight per unit	0.1775 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Rating	120V
Material	Thermoplastic
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Poles	Single Pole
Switch Type	Paddle
Voltage	120/277 V
Voltage Rating	120

Material, Color, and Finish

Color	Nickel
-------	--------

Dimensions and Weight

Size	1.27" Depth x 1.43" Width x 4.19" Height
------	------------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	RADIANT SWITCH 1P 15A 120/277V NICKEL
extra long description	P&S TM870NICC10 RADIANT SWITCH 1P 1
Long Description	NickelDecorator Switch,Single Pole15amp, 120/277VAC with ground, side and, back wire. Our complete line of Decorator devices combine today's design aesthetics with ease of installation, reliability, and performance that never goes out of style.
Product Type	Radiant Switch 1P 15A 120/277V Ni
Special Features	Everyone wants a home that's a step above ordinary. Now the radiant® collection of switches, outlets, dimmers and home automation controls by Legrand puts that stylish finishing touch affordably within reach. radiant gets rid of unsightly screws, delivering clean looks in a range of colors and metallic finishes.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007021059
Manufacturers Part Number	TM870-NICC10
UPC	785007021059

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Decorator Switch

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	10
Weight Per each	0.1775

Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximun continuous +115°C, minimum -40°C
standard	CULUS, UL, CSA Listed, UL Listed