



## BLANK PLATES -- BOX MOUNTED, TWO GANG, LIGHT ALMOND

TP23LA | [Pass & Seymour](#)

### FEATURES & BENEFITS

Trademaster Plate 2gang Blank Box Mount Light Almond



- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Size: Standard  
Type: Box Mount  
Special Features: Unbreakable  
Style: Blank Plate

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121704

UR: No

## DIMENSIONS

Weight: 0.10437

## TECHNICAL INFORMATION

Material: Nylon

Capacity: 2-gang

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant





## BLANK PLATES -- BOX MOUNTED, TWO GANG, LIGHT ALMOND

TP23LA | [Pass & Seymour](#)

### FEATURES & BENEFITS

Trademaster Plate 2gang Blank Box Mount Light Almond



- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Size: Standard  
Type: Box Mount  
Special Features: Unbreakable  
Style: Blank Plate

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121704

UR: No

**DIMENSIONS**

Weight: 0.10437

**TECHNICAL INFORMATION**

Material: Nylon

Capacity: 2-gang

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

