

# Eaton TP274

Catalog Number: TP274

Eaton Crouse-Hinds series Octagon Outlet Box, (5) 1/2", 4", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, 15.5 cubic inch capacity



## General specifications

| Product Name                                 | Catalog Number |
|--|----------------|
| Eaton Crouse-Hinds series octagon outlet box | TP274          |
|  | UPC            |
|  | 786189102741   |
| Product Length/Depth                         | Product Height |
| 4 in   | 1.5 in         |
| Product Width                                | Product Weight |
| 4 in   | 0.5 lb         |

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Depth

1-1/2"

### Capacity

15.5 cubic in

### Conduit/cable

Conduit (no clamps)

### Side knockouts

(4) 1/2 in

### Bottom Knockouts

(5) 1/2 in

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP274](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP274

Catalog Number: TP274

Eaton Crouse-Hinds series Octagon Outlet Box, (5) 1/2", 4", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, 15.5 cubic inch capacity



## General specifications

| Product Name                                 | Catalog Number |
|--|----------------|
| Eaton Crouse-Hinds series octagon outlet box | TP274          |
|  | UPC            |
|  | 786189102741   |
| Product Length/Depth                         | Product Height |
| 4 in   | 1.5 in         |
| Product Width                                | Product Weight |
| 4 in   | 0.5 lb         |

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Depth

1-1/2"

### Capacity

15.5 cubic in

### Conduit/cable

Conduit (no clamps)

### Side knockouts

(4) 1/2 in

### Bottom Knockouts

(5) 1/2 in

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP274](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)