

# Specifications



## Eaton TP286

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 1-1/2", Steel, (2) 1/2", (2) 3/4", Fixture rated, Extension ring, 15.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series octagon outlet box
<b>CATALOG NUMBER</b>	TP286
<b>UPC</b>	786189102864
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	1.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.36 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4"
<b>DEPTH</b>	1-1/2"
<b>CAPACITY</b>	15.5 cubic in
<b>CONDUIT/CABLE</b>	Conduit (no clamps)

<b>SIDE KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in, (2) 3/4 in
<b>MATERIAL</b>	Steel
<b>TYPE</b>	Extension ring
<b>SPECIAL FEATURES</b>	Fixture rated

## Resources

**CATALOGS** [Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

**CERTIFICATION REPORTS** [Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - TP286](#)

[Steel Outlet Boxes for Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TP286

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 1-1/2", Steel, (2) 1/2", (2) 3/4", Fixture rated, Extension ring, 15.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series octagon outlet box
<b>CATALOG NUMBER</b>	TP286
<b>UPC</b>	786189102864
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	1.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.36 lb



Powering Business Worldwide

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4"
<b>DEPTH</b>	1-1/2"
<b>CAPACITY</b>	15.5 cubic in
<b>CONDUIT/CABLE</b>	Conduit (no clamps)

<b>SIDE KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in, (2) 3/4 in
<b>MATERIAL</b>	Steel
<b>TYPE</b>	Extension ring
<b>SPECIAL FEATURES</b>	Fixture rated

## Resources

**CATALOGS** [Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

**CERTIFICATION REPORTS** [Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

**CERTIFICATION REPORTS** [Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - TP286](#)

[Steel Outlet Boxes for Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

