# Specifications



## Eaton TP412

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 1-1/2", Steel, (8) 3/4", 22.0 cubic inch capacity

| General specifications | |
|---|---|
| **PRODUCT NAME** | Eaton Crouse-Hinds series square outlet box |
| **CATALOG NUMBER** | TP412 |
| **UPC** | 786189104127 |
| **PRODUCT LENGTH/DEPTH** | 4 in |
| **PRODUCT HEIGHT** | 1.5 in |
| **PRODUCT WIDTH** | 4 in |
| **PRODUCT WEIGHT** | 0.67 lb |

Powering Business Worldwide

## Certifications and compliances

| | |
|---|---|
| **AREA CLASSIFICATION** | Ordinary/Non-Hazardous Locations |
| **STANDARDS TYPE** | NEC/CEC |

## Product specifications

| | |
|---|---|
| **BOX SIZE** | 4" |
| **CAPACITY** | 22 cubic in |
| **DEPTH** | 1-1/2" |
| **CONDUIT/CABLE** | Conduit (no clamps) |
| **CONSTRUCTION** | Drawn |
| **SIDE KNOCKOUTS** | (8) 3/4 in |
| **BOTTOM KNOCKOUTS** | (3) 1/2 in, (2) 3/4 in |
| **MATERIAL** | Steel |

## Resources

| | |
|---|---|
| CATALOGS | Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page |
| CERTIFICATION REPORTS | 4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification<br>4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification |
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems<br>Eaton Specification Sheet - TP412 |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton TP412

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 1-1/2", Steel, (8) 3/4", 22.0 cubic inch capacity

| General specifications | |
|---|---|
| **PRODUCT NAME** | Eaton Crouse-Hinds series square outlet box |
| **CATALOG NUMBER** | TP412 |
| **UPC** | 786189104127 |
| **PRODUCT LENGTH/DEPTH** | 4 in |
| **PRODUCT HEIGHT** | 1.5 in |
| **PRODUCT WIDTH** | 4 in |
| **PRODUCT WEIGHT** | 0.67 lb |

Powering Business Worldwide

## Certifications and compliances

| | |
|---|---|
| **AREA CLASSIFICATION** | Ordinary/Non-Hazardous Locations |
| **STANDARDS TYPE** | NEC/CEC |

## Product specifications

| | |
|---|---|
| **BOX SIZE** | 4" |
| **CAPACITY** | 22 cubic in |
| **DEPTH** | 1-1/2" |
| **CONDUIT/CABLE** | Conduit (no clamps) |
| **CONSTRUCTION** | Drawn |
| **SIDE KNOCKOUTS** | (8) 3/4 in |
| **BOTTOM KNOCKOUTS** | (3) 1/2 in, (2) 3/4 in |
| **MATERIAL** | Steel |

## Resources

| | |
|---|---|
| CATALOGS | Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page |
| CERTIFICATION REPORTS | 4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification<br>4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification |
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems<br>Eaton Specification Sheet - TP412 |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.