

# Specifications



## Eaton TP412

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 1-1/2", Steel, (8) 3/4", 22.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square outlet box
<b>CATALOG NUMBER</b>	TP412
<b>UPC</b>	786189104127
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	1.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.67 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4"
<b>CAPACITY</b>	22 cubic in
<b>DEPTH</b>	1-1/2"
<b>CONDUIT/CABLE</b>	Conduit (no clamps)

<b>CONSTRUCTION</b>	Drawn
<b>SIDE KNOCKOUTS</b>	(8) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in, (2) 3/4 in
<b>MATERIAL</b>	Steel

## Resources

**CATALOGS** [Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

**CERTIFICATION REPORTS** [4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - TP412](#)

[Steel Outlet Boxes for Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TP412

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 1-1/2", Steel, (8) 3/4", 22.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square outlet box
<b>CATALOG NUMBER</b>	TP412
<b>UPC</b>	786189104127
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	1.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.67 lb



Powering Business Worldwide

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4"
<b>CAPACITY</b>	22 cubic in
<b>DEPTH</b>	1-1/2"
<b>CONDUIT/CABLE</b>	Conduit (no clamps)

<b>CONSTRUCTION</b>	Drawn
<b>SIDE KNOCKOUTS</b>	(8) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in, (2) 3/4 in
<b>MATERIAL</b>	Steel

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification</a> <a href="#">4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - TP412</a> <a href="#">Steel Outlet Boxes for Electrical Systems</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

