

Specifications



Eaton TP436

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 2-1/8", Steel, (8) 1", 30.3 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP436
UPC	786189104363
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.84 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	30.3 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)

CONSTRUCTION	Welded
SIDE KNOCKOUTS	(8) 1 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
MATERIAL	Steel

Resources

CATALOGS [Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS [4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - TP436](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP436

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 2-1/8", Steel, (8) 1", 30.3 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP436
UPC	786189104363
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.84 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	30.3 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)

CONSTRUCTION	Welded
SIDE KNOCKOUTS	(8) 1 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
MATERIAL	Steel

Resources

CATALOGS

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP436](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

