

Specifications



Eaton TP556

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (8) 1/2", (4) 3/4", 42.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP556
UPC	786189105568
PRODUCT LENGTH/DEPTH	4.69 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4.69 in
PRODUCT WEIGHT	1.04 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4-11/16"
CAPACITY	42 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)

CONSTRUCTION	Drawn
SIDE KNOCKOUTS	(8) 1/2 in, (4) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP556 3D drawing](#)

CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP556](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP556

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (8) 1/2", (4) 3/4", 42.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP556
UPC	786189105568
PRODUCT LENGTH/DEPTH	4.69 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4.69 in
PRODUCT WEIGHT	1.04 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4-11/16"
CAPACITY	42 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)

CONSTRUCTION	Drawn
SIDE KNOCKOUTS	(8) 1/2 in, (4) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP556 3D drawing](#)

CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP556](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

