

Specifications



Eaton TP558

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (4) 3/4", (4) 1", 42.0 cubic inch capacity

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series square outlet box |
| CATALOG NUMBER | TP558 |
| UPC | 786189105582 |
| PRODUCT LENGTH/DEPTH | 4.69 in |
| PRODUCT HEIGHT | 2.13 in |
| PRODUCT WIDTH | 4.69 in |
| PRODUCT WEIGHT | 1.04 lb |



Powering Business Worldwide

Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|----------------------|---------------------|
| BOX SIZE | 4-11/16" |
| CAPACITY | 42 cubic in |
| DEPTH | 2-1/8" |
| CONDUIT/CABLE | Conduit (no clamps) |

| | |
|-------------------------|------------------------|
| CONSTRUCTION | Drawn |
| SIDE KNOCKOUTS | (4) 3/4 in, (4) 1 in |
| BOTTOM KNOCKOUTS | (3) 1/2 in, (2) 3/4 in |
| MATERIAL | Steel |

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP558 3D drawing](#)

CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP558](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP558

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (4) 3/4", (4) 1", 42.0 cubic inch capacity

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series square outlet box |
| CATALOG NUMBER | TP558 |
| UPC | 786189105582 |
| PRODUCT LENGTH/DEPTH | 4.69 in |
| PRODUCT HEIGHT | 2.13 in |
| PRODUCT WIDTH | 4.69 in |
| PRODUCT WEIGHT | 1.04 lb |



Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|----------------------|---------------------|
| BOX SIZE | 4-11/16" |
| CAPACITY | 42 cubic in |
| DEPTH | 2-1/8" |
| CONDUIT/CABLE | Conduit (no clamps) |

| | |
|-------------------------|------------------------|
| CONSTRUCTION | Drawn |
| SIDE KNOCKOUTS | (4) 3/4 in, (4) 1 in |
| BOTTOM KNOCKOUTS | (3) 1/2 in, (2) 3/4 in |
| MATERIAL | Steel |

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP558 3D drawing](#)

CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP558](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

