

Eaton TP562

Catalog Number: TP562

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (4) 1-1/4", 42.0 cubic inch capacity



General specifications

| Product Name | Catalog Number |
|---|----------------|
| Eaton Crouse-Hinds series square outlet box | TP562 |
| | UPC |
| | 786189105629 |
| Product Length/Depth | Product Height |
| 4.69 in | 2.13 in |
| Product Width | Product Weight |
| 4.69 in | 1.04 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4-11/16"

Capacity

42 cubic in

Depth

2-1/8"

Conduit/cable

Conduit (no clamps)

Construction

Drawn

Side knockouts

(4) 1-1/4 in

Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

Material

Steel

Resources

3D CAD drawing package

Eaton Crouse-Hinds TP562 3D drawing

Catalogs

Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers
catalog page

Certification reports

4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL
certification

4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings
Canadian certification

Specifications and datasheets

Eaton Specification Sheet - TP562

Steel Outlet Boxes for Electrical Systems



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP562

Catalog Number: TP562

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (4) 1-1/4", 42.0 cubic inch capacity



General specifications

| Product Name | Catalog Number |
|---|----------------|
| Eaton Crouse-Hinds series square outlet box | TP562 |
| | UPC |
| | 786189105629 |
| Product Length/Depth | Product Height |
| 4.69 in | 2.13 in |
| Product Width | Product Weight |
| 4.69 in | 1.04 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4-11/16"

Capacity

42 cubic in

Depth

2-1/8"

Conduit/cable

Conduit (no clamps)

Construction

Drawn

Side knockouts

(4) 1-1/4 in

Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

Material

Steel

Resources

3D CAD drawing package

Eaton Crouse-Hinds TP562 3D drawing

Catalogs

Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers
catalog page

Certification reports

4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL
certification

4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings
Canadian certification

Specifications and datasheets

Eaton Specification Sheet - TP562

Steel Outlet Boxes for Electrical Systems



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)