

---

## TOGGLE SWITCH OPENINGS, FIVE GANG, IVORY

TP51 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Trademaster Plate 5gang 5toggle Ivory



- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Size: Standard  
Type: Toggle

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121704  
UR: No

## DIMENSIONS

Depth (US): 12.5

Width (US): 5

Volume: 18.75

Weight: 0.19885

Height: 0.3

## TECHNICAL INFORMATION

Material: Plastic

Capacity: 5-gang

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant



---

## TOGGLE SWITCH OPENINGS, FIVE GANG, IVORY

TP51 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Trademaster Plate 5gang 5toggle Ivory



- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Size: Standard  
Type: Toggle

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121704  
UR: No

## DIMENSIONS

Depth (US): 12.5

Width (US): 5

Volume: 18.75

Weight: 0.19885

Height: 0.3

## TECHNICAL INFORMATION

Material: Plastic

Capacity: 5-gang

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

