

# Specifications



## Eaton TP604

Eaton Crouse-Hinds series Utility Box, (3) 1/2", 2-1/8", Steel, (8) 1/2", 14.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series utility box
<b>CATALOG NUMBER</b>	TP604
<b>UPC</b>	786189106046
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	2.13 in
<b>PRODUCT WIDTH</b>	2.13 in
<b>PRODUCT WEIGHT</b>	0.56 lb



*Powering Business Worldwide*

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>DEPTH</b>	2-1/8"
<b>CAPACITY</b>	14.5 cubic in
<b>SIDE KNOCKOUTS</b>	(8) 1/2 in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in

**Resources**

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Utility Boxes and Covers catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Utility Boxes and Covers Canadian certification</a> <a href="#">Steel Utility Boxes and Covers UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP604</a>

---

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TP604

Eaton Crouse-Hinds series Utility Box, (3) 1/2", 2-1/8", Steel, (8) 1/2", 14.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series utility box
<b>CATALOG NUMBER</b>	TP604
<b>UPC</b>	786189106046
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	2.13 in
<b>PRODUCT WIDTH</b>	2.13 in
<b>PRODUCT WEIGHT</b>	0.56 lb



*Powering Business Worldwide*

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>DEPTH</b>	2-1/8"
<b>CAPACITY</b>	14.5 cubic in
<b>SIDE KNOCKOUTS</b>	(8) 1/2 in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in

**Resources**

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Utility Boxes and Covers catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Utility Boxes and Covers Canadian certification</a> <a href="#">Steel Utility Boxes and Covers UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP604</a>

---

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

