

# Eaton TP582

Catalog Number: TP582

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, one device, Steel, 1-1/4" raised, 8.5 cubic inch capacity



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square cover	TP582
UPC	Product Length/Depth
786189105827	4.69 in
Product Height	Product Width
1.25 in	4.69 in
Product Weight	
0.52 lb	

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4-11/16"

### Capacity

8.5 cubic in

### Color

Natural

### Configuration

Raised surface, one device

### Material

Steel

### Type

1-1/4" raised

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds TP582 3D drawing](#)

### Catalogs

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP582](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP582

Catalog Number: TP582

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, one device, Steel, 1-1/4" raised, 8.5 cubic inch capacity



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square cover	TP582
UPC	Product Length/Depth
786189105827	4.69 in
Product Height	Product Width
1.25 in	4.69 in
Product Weight	
0.52 lb	

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4-11/16"

### Capacity

8.5 cubic in

### Color

Natural

### Configuration

Raised surface, one device

### Material

Steel

### Type

1-1/4" raised

## Resources

### 3D CAD drawing package

Eaton Crouse-Hinds TP582 3D drawing

### Catalogs

Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers  
catalog page

### Certification reports

4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL  
certification

4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings  
Canadian certification

### Specifications and datasheets

Steel Outlet Boxes for Electrical Systems

Eaton Specification Sheet - TP582



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)