

# Eaton TP622

Catalog Number: TP622

Eaton Crouse-Hinds series Octagon Concrete Box, 4", 2-1/2", Steel, 1/2" and 3/4" single row, 29.0 cubic inch capacity

## General specifications



Photo is representative

|  |                       |
|--|-----------------------|
| <b>Product Name</b>                            | <b>Catalog Number</b> |
| Eaton Crouse-Hinds series octagon concrete box | TP622                 |
|  | <b>UPC</b>            |
|  | 786189106220          |
| <b>Product Length/Depth</b>                    | <b>Product Height</b> |
| 4 in   | 2.5 in                |
| <b>Product Width</b>                           | <b>Product Weight</b> |
| 4 in   | 0.72 lb               |

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Material

Steel

### Box size

4"

### Depth

2-1/2"

### Side knockouts

1/2 in and 3/4 in single row

### Capacity

29 cubic in

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Octagon Concrete Boxes catalog page](#)

### Certification reports

[4-Inch Steel Octagon Concrete Boxes UL certification](#)

[4-Inch Steel Octagon Concrete Boxes Canadian certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP622](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP622

Catalog Number: TP622

Eaton Crouse-Hinds series Octagon Concrete Box, 4", 2-1/2", Steel, 1/2" and 3/4" single row, 29.0 cubic inch capacity

## General specifications



Photo is representative

|  |                       |
|--|-----------------------|
| <b>Product Name</b>                            | <b>Catalog Number</b> |
| Eaton Crouse-Hinds series octagon concrete box | TP622                 |
|  | <b>UPC</b>            |
|  | 786189106220          |
| <b>Product Length/Depth</b>                    | <b>Product Height</b> |
| 4 in   | 2.5 in                |
| <b>Product Width</b>                           | <b>Product Weight</b> |
| 4 in   | 0.72 lb               |

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Material

Steel

### Box size

4"

### Depth

2-1/2"

### Side knockouts

1/2 in and 3/4 in single row

### Capacity

29 cubic in

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Octagon Concrete Boxes catalog page](#)

### Certification reports

[4-Inch Steel Octagon Concrete Boxes UL certification](#)

[4-Inch Steel Octagon Concrete Boxes Canadian certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP622](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)