

# Specifications



Photo is representative

## Eaton TP678

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Conduit (no clamps), 2-3/4", (1) 3/4", Steel, (1) 3/4", Ears, Gangable, 14.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series switch box
<b>CATALOG NUMBER</b>	TP678
<b>UPC</b>	786189106787
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	2.75 in
<b>PRODUCT WEIGHT</b>	0.61 lb

**EATON**

*Powering Business Worldwide*

### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**DEPTH** 2-3/4"

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC

<b>TYPE</b>	Gangable
<b>CAPACITY</b>	14 cubic in
<b>CONDUIT/CABLE</b>	Conduit (no clamps)
<b>END KNOCKOUTS</b>	(1) 3/4 in
<b>SIDE KNOCKOUTS</b>	(1) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(1) 1/2 in
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Ears

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Switch Boxes catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Switch Boxes Canadian certification</a> <a href="#">Steel Switch Boxes UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP678</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative

## Eaton TP678

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Conduit (no clamps), 2-3/4", (1) 3/4", Steel, (1) 3/4", Ears, Gangable, 14.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series switch box
<b>CATALOG NUMBER</b>	TP678
<b>UPC</b>	786189106787
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	2.75 in
<b>PRODUCT WEIGHT</b>	0.61 lb

**EATON**

*Powering Business Worldwide*

### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**DEPTH** 2-3/4"

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC

<b>TYPE</b>	Gangable
<b>CAPACITY</b>	14 cubic in
<b>CONDUIT/CABLE</b>	Conduit (no clamps)
<b>END KNOCKOUTS</b>	(1) 3/4 in
<b>SIDE KNOCKOUTS</b>	(1) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(1) 1/2 in
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Ears

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Switch Boxes catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Switch Boxes Canadian certification</a> <a href="#">Steel Switch Boxes UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP678</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

