

Specifications




Photo is representative

Eaton TP683

Eaton Crouse-Hinds series Masonry Box, (4) 1/2", (4) 3/4", 2-1/2", (2) 1/2", (2) 3/4", Steel, Two-gang, (2) 1/2", (2) 3/4", 31.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series masonry box
CATALOG NUMBER	TP683
UPC	786189106831
PRODUCT LENGTH/DEPTH	3.75 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	3.75 in
PRODUCT WEIGHT	1.03 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

DEPTH 2-1/2"

	Locations
STANDARDS TYPE	NEC/CEC

NUMBER OF GANGS	Two-gang
END KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(4) 1/2 in, (4) 3/4 in
CAPACITY	31 cubic in
MATERIAL	Steel

Resources

CATALOGS

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

CERTIFICATION REPORTS

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP683](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications




Photo is representative

Eaton TP683

Eaton Crouse-Hinds series Masonry Box, (4) 1/2", (4) 3/4", 2-1/2", (2) 1/2", (2) 3/4", Steel, Two-gang, (2) 1/2", (2) 3/4", 31.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series masonry box
CATALOG NUMBER	TP683
UPC	786189106831
PRODUCT LENGTH/DEPTH	3.75 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	3.75 in
PRODUCT WEIGHT	1.03 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

DEPTH 2-1/2"

	Locations
STANDARDS TYPE	NEC/CEC

NUMBER OF GANGS	Two-gang
END KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(4) 1/2 in, (4) 3/4 in
CAPACITY	31 cubic in
MATERIAL	Steel

Resources

CATALOGS

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

CERTIFICATION REPORTS

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP683](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

