


# Specifications

## Eaton TP693

Eaton Crouse-Hinds series Masonry Box, (8) 1/2", (8) 3/4", 3-1/2", (8) 1/2", (8) 3/4", Steel, Four-gang, (2) 1/2", (2) 3/4", 88.0 cubic inch capacity



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series masonry box
<b>CATALOG NUMBER</b>	TP693
<b>UPC</b>	786189106930
<b>PRODUCT LENGTH/DEPTH</b>	7.38 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	2.07 lb



Powering Business Worldwide

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

## Product specifications

DEPTH	3-1/2"
NUMBER OF GANGS	Four-gang
END KNOCKOUTS	(8) 1/2 in, (8) 3/4 in
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(8) 1/2 in, (8) 3/4 in
CAPACITY	88 cubic in
MATERIAL	Steel

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Steel Masonry Boxes catalog page</a>
CERTIFICATION REPORTS	<a href="#">Steel Masonry Boxes Canadian certification</a> <a href="#">Steel Masonry Boxes UL certification</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TP693</a> <a href="#">Steel Outlet Boxes for Electrical Systems</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.


Follow us on social media to get the latest product and support information.



# Specifications

## Eaton TP693

Eaton Crouse-Hinds series Masonry Box, (8) 1/2", (8) 3/4", 3-1/2", (8) 1/2", (8) 3/4", Steel, Four-gang, (2) 1/2", (2) 3/4", 88.0 cubic inch capacity



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series masonry box
<b>CATALOG NUMBER</b>	TP693
<b>UPC</b>	786189106930
<b>PRODUCT LENGTH/DEPTH</b>	7.38 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	2.07 lb



Powering Business Worldwide

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

## Product specifications

DEPTH	3-1/2"
NUMBER OF GANGS	Four-gang
END KNOCKOUTS	(8) 1/2 in, (8) 3/4 in
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(8) 1/2 in, (8) 3/4 in
CAPACITY	88 cubic in
MATERIAL	Steel

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Steel Masonry Boxes catalog page</a>
CERTIFICATION REPORTS	<a href="#">Steel Masonry Boxes Canadian certification</a> <a href="#">Steel Masonry Boxes UL certification</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TP693</a> <a href="#">Steel Outlet Boxes for Electrical Systems</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

