

Eaton TP692

Catalog Number: TP692

Eaton Crouse-Hinds series Masonry Box, (6) 1/2", (6) 3/4", 3-1/2", (6) 1/2", (6) 3/4", Steel, Three-gang, (2) 1/2", (2) 3/4", 66.5 cubic inch capacity

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series masonry box	TP692
UPC	Product Length/Depth
786189106923	5.56 in
Product Height	Product Width
3.75 in	3.75 in
Product Weight	
1.55 lb	

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Depth

3-1/2"

Number of gangs

Three-gang

End Knockouts

(6) 1/2 in, (6) 3/4 in

Side knockouts

(2) 1/2 in, (2) 3/4 in

Bottom Knockouts

(6) 1/2 in, (6) 3/4 in

Capacity

66.5 cubic in

Material

Steel

Resources

Catalogs

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

Certification reports

[Steel Masonry Boxes UL certification](#)

[Steel Masonry Boxes Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP692](#)

[Steel Outlet Boxes for Electrical Systems](#)

Eaton Corporation plc

Eaton House

30 Pembroke Road

Dublin 4, Ireland

Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP692

Catalog Number: TP692

Eaton Crouse-Hinds series Masonry Box, (6) 1/2", (6) 3/4", 3-1/2", (6) 1/2", (6) 3/4", Steel, Three-gang, (2) 1/2", (2) 3/4", 66.5 cubic inch capacity

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series masonry box	TP692
UPC	Product Length/Depth
786189106923	5.56 in
Product Height	Product Width
3.75 in	3.75 in
Product Weight	
1.55 lb	

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Depth

3-1/2"

Number of gangs

Three-gang

End Knockouts

(6) 1/2 in, (6) 3/4 in

Side knockouts

(2) 1/2 in, (2) 3/4 in

Bottom Knockouts

(6) 1/2 in, (6) 3/4 in

Capacity

66.5 cubic in

Material

Steel

Resources

Catalogs

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

Certification reports

[Steel Masonry Boxes UL certification](#)

[Steel Masonry Boxes Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP692](#)

[Steel Outlet Boxes for Electrical Systems](#)

Eaton Corporation plc

Eaton House

30 Pembroke Road

Dublin 4, Ireland

Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)