



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR5262USBBK Dup Rec 15A TR Spec W/3.1A Usb CHRG BK

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | TR5262USBBK  |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Designed For Commercial Markets With Strength and Durability In Mind, This Combination Duplex Receptacle and Two Usb Type-A Features 3.1A Overall Usb Charging Capability and Is Compatible With Usb 2.0 & 3.0 Devices. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page. |
| Weight per unit  | 0.3392 (lbs/each)  |
| Product Category | Combination Devices  |

### Features

|                     |  |
|---------------------|--|
| amperage rating     | 15   |
| connection          | Side & Back Wired                                  |
| Dielectric Strength | Withstands 2000V minimum                           |
| indoor/outdoor      | Indoor   |
| Number of Wires     | 3  |
| Outlet Type         | Commercial, Tamper-Resistant, Indoor, USB-Charging |
| Phase               | 1  |
| Poles               | Double Pole  |
| Voltage             | 125.0 V  |
| Voltage Rating      | 125  |
| Wire Size           | 14 - 10  |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Finish | Matte |
|--------|-------|

### Dimensions and Weight

|        |       |
|--------|-------|
| Depth  | 1.392 |
| Height | 3.281 |
| Width  | 1.693 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | DUP REC 15A TR SPEC W/3.1A USB CHRG BK   |
| extra long description | P&S TR5262USBBK DUP REC 15A TR SPEC  |
| Features               | USB-A Charging   |
| Long Description       | Designed for commercial markets with strength and durability in mind, this combination duplex receptacle and two USB Type-A features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page. |
| Product Type           | Dup Rec 15A TR Spec W/3.1A Usb CHRG BK   |
| Special Features       | Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.   |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | Pass & Seymour/Legrand |
| GTIN                      | 00785007031690         |
| Manufacturers Part Number | TR5262USBBK            |
| UPC                       | 785007031690           |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type                 | Outlet   |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 50     |
| Weight Per each | 0.3392 |

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Commercial   |
| environmental conditions | UL94 V2  |
| Mounting                 | BOX  |
| nema rating              | 5-15R  |
| standard                 | CULUS, UL, FEDSPEC, CSA Listed, cULus, FSUL, UL Listed, RoHS |