



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5362USBW Duplex Recp 20A TR Spec W/3.1A Usb Charge WH

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | TR5362USBW |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Duplex Receptacle, 2 Poles, 20 A, 125 V, #14 to #10 Awg Wire Size, White, 3 Wires, Thermoplastic, 1.392 (D) X 1.693 (W) X 3.281 (H) In, Box Mount, -40 °C Operating Temperature, +60 °C Operating Temperature, 0.34 LB |
| Weight per unit | 0.3392 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|---------------------|--------------------------------|
| amperage rating | 20 |
| connection | Side & Back Wired |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Outlet Type | Tamper-Resistant, USB-Charging |
| Phase | 1 |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|-------|
| Depth | 1.392 |
| Height | 3.281 |
| Width | 1.693 |

Descriptions

| | |
|------------------------|--|
| Description | DUPLEX RECP 20A TR SPEC W/3.1A USB CHARGE WH |
| extra long description | P&S TR5362USBW DUP REC 20A TR SPEC |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007031669 |
| UPC | 785007031669 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Miscellaneous residential devices |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.3392 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Commercial |
| environmental conditions | UL94 V2 |
| Mounting | BOX |
| standard | CULUS, UL, CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC |