



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253



TSD4FBL3PTC Toggle Slide Dimmer 0-10V FL/Led Tri-Color

Pass & Seymour/Legrand

Catalog Number	TSD4FBL3PTC
Manufacturer	Pass & Seymour/Legrand
Description	<P>Trademaster Registered Toggle Slide Dimmer Offers A Solution For Your Residential Led or Fluorescent Lighting Needs. This Single Pole 3-Way Switch Can Be Used In A Two-Location Layout. The Slide Can Be Set to Your Preferred Level and Then Toggle On and Off Providing Instant Repeatability. </P>
Weight per unit	0.2438 (lbs/each)
Product Category	Lighting Dimmers

Features

indoor/outdoor	Indoor
Load Rating	277V 5A (Fluorescent), 120V 10A (Fluorescent), 277V 5A (LED), 120V 10A (LED)
Load Type	LED, Fluorescent
Mounting Type	Wall Box
Number of Gangs	1.0
Number of Switches	1.0
Poles	1
Switch Type	Rocker, Slider
Voltage	0 to 10 V
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Ivory, Light Almond, White
Finish	Matte

Descriptions

Description	TOGGLE SLIDE DIMMER 0-10V FL/LED TRI-COLOR
extra long description	P&S TSD4FBL3PTC TOGGLE SLIDE DIMMER
Features	Preset
Long Description	<p>TradeMaster Registered Toggle Slide Dimmer offers a solution for your residential LED or fluorescent lighting needs. This single pole 3-way switch can be used in a two-location layout. The slide can be set to your preferred level and then toggle on and off providing instant repeatability. </p>
Product Type	Toggle Slide Dimmer 0-10V FL/Led Tri
Special Features	Preset



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007216981
Manufacturers Part Number	TSD4FBL3PTC
UPC	785007216981

Trade Size

Amperage	10.0
----------	------

Packaging

Carton	1
Package	24
Weight Per each	0.2438