

Specification Sheet

Part Number: TSRI-JB2



Article Number

250-10005

Type

TSR-JB2

Color

Ivory (IV)

Features & Benefits

- Tamper resistant, self-locking hidden positive latch permits quick re-entry as well as providing a secure installation of premise wire.
- Fittings incorporate a minimum 1" bend radius per ANSI/TIA-568-C and 569-A standards.
- Rubber-based, foam-tape adhesive with high ultimate bond strength conforms to any surface.
- Flexible hinge allows the raceway to endure numerous openings without creating discoloration or stress cracking

Quantity Per

bag

Product Description

Offered in dual or single gang format, HellermannTyton's Low Voltage Junction Boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSR size of raceway to eliminate routing and installation inconvenience. All junction boxes come with adhesive strips on the back of the base and #6 screws to secure the box to the base.

Short Description

Single Gang Junction Box, 2" Deep, PVC, Ivory, 1/bag

Global Part Name

TSR-JB2-PVC-BGE

Length L (Imperial)

4.75

Length L (Metric)

120.65

Width W (Imperial)

3.0

Width W (Metric)

76.2

Height H (Imperial)

2.0

Height H (Metric)

50.80

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

UL 94 V0

Halogen free

No

Operating Temperature (Metric)

+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

3925900000

Specification Sheet

Part Number: TSRI-JB2



Article Number

250-10005

Type

TSR-JB2

Color

Ivory (IV)

Features & Benefits

- Tamper resistant, self-locking hidden positive latch permits quick re-entry as well as providing a secure installation of premise wire.
- Fittings incorporate a minimum 1" bend radius per ANSI/TIA-568-C and 569-A standards.
- Rubber-based, foam-tape adhesive with high ultimate bond strength conforms to any surface.
- Flexible hinge allows the raceway to endure numerous openings without creating discoloration or stress cracking

Quantity Per

bag

Product Description

Offered in dual or single gang format, HellermannTyton's Low Voltage Junction Boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSR size of raceway to eliminate routing and installation inconvenience. All junction boxes come with adhesive strips on the back of the base and #6 screws to secure the box to the base.

Short Description

Single Gang Junction Box, 2" Deep, PVC, Ivory, 1/bag

Global Part Name

TSR-JB2-PVC-BGE

Length L (Imperial)

4.75

Length L (Metric)

120.65

Width W (Imperial)

3.0

Width W (Metric)

76.2

Height H (Imperial)

2.0

Height H (Metric)

50.80

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

UL 94 V0

Halogen free

No

Operating Temperature (Metric)

+122°F (+50°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

3925900000